

DATA SHEET

I/O cable

Hirose 6-pin female to open end, 5.0 m

Order code:


9437

V1.0.0

2016-Sep-28

Compatible camera family

Mako U





Connector 1

HR10A-7P-6S(73) connector


Cable

Connector 2


Open end: shield and wire
tinned and soldered



Cable label



Wiring diagram



Notes

Unit in technical drawings is [mm].

All shielded pairs connect to shield wire.

Specifications

Feature	Specification
Length	5.0 m ± 100 mm
Diameter	4.9 mm
Classification	Industrial suitability for static applications
Static bending radius	29.4 mm
Dynamic bending radius	For static applications only
Temperature range	On request
Compliance	UL20276, RoHS 2011/65/EU, REACH